



Model T360 Gas Filter Correlation CO₂ Analyzer

The Model T360 CO₂ analyzer measures Carbon Dioxide by comparing infrared energy absorbed by a sample to that absorbed by a reference gas according to the Beer-Lambert law. Using a Gas Filter Correlation Wheel, a high-energy IR light source is alternately passed through a CO₂ filled chamber and a chamber with no CO₂ present. The light path then travels through the sample cell, which has a folded path of 2.56 meters.

The energy loss through the sample cell is compared with the reference signal provided by the filter wheel to produce a signal proportional to concentration, with little effect from interfering gases within the sample. This design produces excellent zero and span stability and a high signal-to-noise ratio, allowing excellent performance over a wide concentration range.

All T Series instruments offer an advanced color display, capacitive touch screen, intuitive user interface, flexible I/O, and built-in data acquisition capability. All instrument set up, control and access to stored data and diagnostic information is available through the front panel, or via RS232, Ethernet, or USB com ports either locally or by remote connection using the included APIcom™ software.

- Ranges: 0-2 ppm to 0-2,000 ppm, user selectable
- Dual ranges and auto ranging
- Large, vivid, and durable color graphics display with touch screen interface
- Ethernet, RS-232, and (optional) USB com ports
- Front panel USB connections for peripheral devices and firmware upgrades
- 8 analog inputs (optional)
- Adaptive signal filtering optimizes response time
- Temperature & pressure compensation
- Comprehensive internal data logging with programmable averaging periods
- Ability to log virtually any operating parameter
- Two-year warranty
- Five-year warranty on GFC wheel

Model T360 Gas Filter Correlation CO₂ Analyzer

Specifications

ectable), ed

How to Order

Model T360 includes:

- Two-year warranty, five-year on GFC wheel
- Internal pump
- · Dual ranges and auto ranging
- 47mm diameter particulate filter
- · 8 isolated digital outputs
- · 6 isolated digital inputs
- · RS-232 ports
- Multi-drop RS232
- Ethernet port
- USB ports for peripheral devices
- APIcom™remote control software
- Select AC input voltage:
 □ 100V 120V □ 50Hz
 □ 220V 240V □ 60Hz
- Select DC output voltage:

 □ 10V
 □ 5V
- □ 1V □ 0.1V

Mounting Options:

- Rack mount brackets with chassis slides
- □ Rack mount brackets only

I/O Options:

- 4-20mA outputs (up to three channels)
- □ USB com port
- □ 8 Analog Inputs
- □ RS485

Other Options:

- □ Concentration alarm relays
- □ Consumables kit
- □ External Pump and Fittings
- □ O₂ 0-25% Paramagnetic sensor
- ☐ CO₂ 0-20% NDIR

The values expressed above are in accordance with EPA definitions. All error specifications are based on constant conditions.

Specifications exceed US EPA and Eignungsgeprüft requirements. Specifications subject to change without notice. Printed documents are uncontrolled.



A Teledyne Technologies Company

35 Inverness Dr. East, Englewood, Colorado 80112-5412 Phone: 303-792-3300 Fax: 303-799-1409 Email: tml_sales@teledyne.com

For more information about Teledyne ML family of monitoring instrumentation products, call us or visit our website at:

www.teledyne-ml.com

Teledyne Monitor Labs, Inc. reserves the right to make changes in construction, design, specifications and/or prices without prior notice.